

Coaxial Panel Connector 22_BNO-0-0-2/133_N

Description

Straight bulkhead receptacle jack

Interface standards
IEC 60169-22



Technical Data

Electrical Data

Impedance not defined Ω
Interface frequency max. 0.2 GHz

Mechanical Data

Chassis torque 2 Nm
Number of matings 500
Weight 0.0063 kg

Environmental Data

Operating temperature -50 °C to 125 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00011411
Catalogue drawing DCA-00011413
Mounting hole DOU-00008762

Ordering Information

Single package 22_BNO-0-0-2/133_NE