

Coaxial Cable Connector 25_716-50-0-2/003_-

Description

Straight panel cable jack, flange mount

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	7.5 GHz		
Frequency range	DC to 1 GHz	1 to 2.5 GHz	2.5 to 5 GHz
Return loss	24.9 dB	20 dB	14 dB

Mechanical Data

Weight	0.1239 kg
--------	-----------

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze / Brass	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00009801
Catalogue drawing	DCA-00009803
Mounting hole	DOU-00008824

Ordering Information

Single package	25_716-50-0-2/003_-E
----------------	----------------------

Additional Information