

Coaxial PCB Connector 82_MCX-75-0-5/111_N

Description

Straight PCB jack

Interface Standards
SUHNER-MCX75



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0007 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012964
Catalogue drawing DCA-00012966

Ordering Information

Bulk 100 pcs package 82_MCX-75-0-5/111_NH

Remarks

PCB connector with stand-offs