



RADIO FREQUENCY
11_N-50-4-72/133_NE

LOW AND HIGH VOLTAGE



Enlarge image



Distributor Availability

Distributor	In Stock
RICHARDSON	0 PC *

Stock levels are subject to change

* Available with lead time

HUBER+SUHNER Lead Time (EXW)

Quantity	Lead Time
> 1 PC	10 WEEKS

Item no.:	85128376
Datasheet:	
Description:	Straight cable plug
Interface:	N





RADIO FREQUENCY

Assembly instruction:



3D model:



LOW AND HIGH VOLTAGE

Picture:



Frequency Range 1:

.1 GHz to 2 GHz

Electrical data



Impedance (Ohm):

50

Interface freq. max. (GHz):

11

Return Loss[-dB]1:

31 DB

VSWR1:

1,06

Frequency Range 2:

2 GHz to 4 GHz

Return Loss[-dB]2:

26,6 DB

VSWR2:

1,1

Frequency Range 3:

4 GHz to 6 GHz

Return Loss[-dB]3:

25,8 DB

VSWR3:

1,11

Mechanical data



Number of matings:

500

Cable entry centre contact:

crimped

Cable entry outer contact:

crimped

Dielectric size:

4 mm



Weight:

0,0254 kg



RADIO FREQUENCY

Material data



LOW AND HIGH VOLTAGE

Ordering information



Available packagings:

Single

Fiber optics

Cables

Connectors

Adapters

Accessories

Assembly & Cable systems

