

Coaxial Panel Connector 23_SMA-50-0-94/199_N

Description

Straight panel receptacle jack, flange mount

Interface standards
SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 26.5 GHz |

Mechanical Data

| | |
|-------------------|-----------|
| Number of matings | 500 |
| Weight | 0.0029 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 125 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Stainless Steel | |
| Body | Stainless Steel | |
| Insulator | PFA / PTFE | |

Related Documents

| | |
|-------------------|--------------|
| Catalogue drawing | DCA-00011332 |
| Mounting hole | DOU-00010189 |

Ordering Information

| | |
|----------------|-----------------------|
| Single package | 23_SMA-50-0-94/199_NE |
|----------------|-----------------------|