

Coaxial Cable Connector 21_N-50-7-13/133_N

Description

Straight cable jack

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0371 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00007137
Catalogue drawing	DCA-00066594
Assembly instruction	DOC-0000179092

Ordering Information

Single package	21_N-50-7-13/133_NE
----------------	---------------------

Additional Information

Suitable cables	RG_213_/U, GX_07272, G_07262, G_07272, RADOX_RF_213
-----------------	---