

Coaxial Panel Connector 23_716-50-0-1/003_-

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz

Mechanical Data

Number of matings	500
Weight	0.0793 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze / Brass	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00010010
Catalogue drawing	DCA-00011200
Mounting hole	DOU-00008824

Ordering Information

Single package	23_716-50-0-1/003_-E
----------------	----------------------