

Coaxial PCB Connector 82_MMBX-50-0-14/111_N

Description

Straight PCB jack

Interface Standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 12.4 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0007 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing DOU-00002008
Mounting hole DOU-00002008

Ordering Information

Bulk 100 pcs package 82_MMBX-50-0-14/111_NH
Single package 82_MMBX-50-0-14/111_NE
Tape and Reel package 82_MMBX-50-0-14/111_NM

Remarks

PCB connector with stand-offs