Data Sheet

HUBER+SUHNER

Coaxial Cable Connector 11_QLA-01-3-1/122_N

Description

Straight cable plug

Interface standards NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data Impedance Interface frequency max.	50 Ω 1.4 GHz
Mechanical Data Centre contact Outer contact Weight	crimped crimped 0.0054 kg
Environmental Data Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-55 °C to 150 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	
Assembly instruction	

Ordering Information

Single package

11_QLA-01-3-1/122_NE

DOU-00006540 DOC-0000180108

Additional Information

Suitable cables

RG_58_C/U, G_03232, GX_03272

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.