

Coaxial PCB Connector 82_MCX-50-0-17/111_N_-1

Description

Straight PCB jack

Interface Standards
IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0007 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012981
Catalogue drawing DCA-00012983

Ordering Information

Bulk 100 pcs package 82_MCX-50-0-17/111_NH-1

Remarks

PCB connector without stand-offs