Data Sheet



Coaxial PCB Connector 82_MMCX-S50-0-2/111_K

Description

Straight PCB jack

Interface Standards
SUHNER-MMCX



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 6 \ \text{GHz} \end{array}$

Mechanical Data

Board mounting type edge mount Weight 0.0007 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -55 °C to 155 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00013081
Catalogue drawing DCA-00013083

Ordering Information

 Bulk 100 pcs package
 82_MMCX-S50-0-2/111_KH

 Tape and Reel package
 82_MMCX-S50-0-2/111_KG

 Single package
 82_MMCX-S50-0-2/111_KE