# **Data Sheet**

## Coaxial PCB Connector 82\_MMBX-50-0-14/111\_N

#### Description

Straight PCB jack

Interface Standards SUHNER-MMBX

# HUBER+SUHNER



### **Technical Data**

Electrical Data Impedance Interface frequency max.	50 Ω 12.4 GHz	
Mechanical Data		
Board mounting type	through holes	
Weight	0.0007 kg	
Environmental Data		
Operating temperature	-55 °C to 155 °C	
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant	
Material Data		
Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating

Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

#### **Related Documents**

Outline drawing	DOU-00002008
Mounting hole	DOU-00002008

#### **Ordering Information**

Bulk 100 pcs package	82_MMBX-50-0-14/111_NH
Single package	82_MMBX-50-0-14/111_NE
Tape and Reel package	82_MMBX-50-0-14/111_NM

### Remarks

PCB connector with stand-offs

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.