Data Sheet

Coaxial Panel Connector 22_SMB-50-0-2/111_N

Description

Straight bulkhead receptacle jack

Interface standards IEC 60169-10_MIL-STD-348A/311_CECC 22130

Technical Data

Electrical Data Impedance Interface frequency max.	50 Ω 4 GHz
Mechanical Data Number of matings Weight	500 0.0012 kg
Environmental Data Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102) Material Data	compliant

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)

Related Documents

Outline drawing	DOU-00010650
Catalogue drawing	DCA-00010652
Mounting hole	DOU-00008855

Ordering Information

Single package

22_SMB-50-0-2/111_NE

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.

