

## Within Series Adaptor 32\_MMBX-50-0-13/111\_N

### Description

Adaptor plug/plug  
MMBX plug (male) / MMBX plug (male)

Slide - snap interface

Interface standard  
Series MMBX - SUHNER-MMBX



### Technical Data

#### Electrical Data

|                          |               |              |               |
|--------------------------|---------------|--------------|---------------|
| Impedance                | 50 Ω          |              |               |
| Interface frequency max. | 12.4 GHz      |              |               |
| Frequency range          | DC to 2.5 GHz | 2.5 to 6 GHz | 6 to 12.4 GHz |
| Return loss              | ≥ 32 dB       | ≥ 26 dB      | ≥ 15 dB       |

#### Mechanical Data

|                   |           |
|-------------------|-----------|
| Number of matings | 100       |
| Weight            | 0.0004 kg |

#### Environmental Data

|  |                  |
|--|------------------|
| Operating temperature                                | -55 °C to 155 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

Interface - MMBX plug (male)

| Piece Parts    | Material               | Surface Plating |
|----------------|------------------------|-----------------|
| Centre contact | Copper Beryllium Alloy | SUCOPRO Plating |
| Outer contact  | Bronze                 | SUCOPRO Plating |
| Body           | Bronze                 | SUCOPRO Plating |
| Insulator      | PFA / PTFE             |                 |

Interface - MMBX plug (male)

| Piece Parts    | Material               | Surface Plating |
|----------------|------------------------|-----------------|
| Centre contact | Copper Beryllium Alloy | SUCOPRO Plating |
| Outer contact  | Bronze                 | SUCOPRO Plating |
| Body           | Bronze                 | SUCOPRO Plating |
| Insulator      | PFA / PTFE             |                 |

### Related Documents

|                 |              |
|-----------------|--------------|
| Outline drawing | DOU-00064707 |
|-----------------|--------------|

### Ordering Information

|                      |                        |
|----------------------|------------------------|
| Single package       | 32_MMBX-50-0-13/111_NE |
| Bulk 100 pcs package | 32_MMBX-50-0-13/111_NH |
| Tray package         | 32_MMBX-50-0-13/111_NY |