

Coaxial Cable Connector 16_MM CX-50-1-12/111_O

Description

Right angle cable plug

Interface standards

SUHNER-MM CX

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact soldered
Outer contact soldered
Weight 0.0003 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|--|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | Gold Plating (without Nickel underplating) |
| Body | Brass | Gold Plating (without Nickel underplating) |
| Insulator | PFA / PTFE | |

Related Documents

Outline drawing DOU-00007190
Catalogue drawing DCA-00094523
Assembly instruction DOC-0000180777

Ordering Information

Bulk 100 pcs package 16_MM CX-50-1-12/111_OH
Single package 16_MM CX-50-1-12/111_OE

Additional Information

Suitable cables EZ_47_TP_M17, SUCOFORM_47_CU