

Coaxial Cable Connector 11_BNC-50-3-4/133_N

Description

Straight cable plug

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0103 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006208
Catalogue drawing	DCA-00006196
Assembly instruction	DOC-0000179061

Ordering Information

Bulk 100 pcs package	11_BNC-50-3-4/133_NH
Single package	11_BNC-50-3-4/133_NE

Additional Information

Suitable cables	RG_58_C/U, GX_03272
-----------------	---------------------