

Between Series Adaptor 33_MMPX-SK-50-1/199_N

Description

Adaptor plug/jack
MMPX plug (male) / SK jack (female)

Precision adaptor
For Test & Measurement applications

Interface standards
Series MMPX - HUBER+SUHNER MMPX STD (Patent US 7.294.023)
Series SK - MIL-STD-348A/323



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	40 GHz		
Frequency range	DC to 15 GHz	15 to 30 GHz	30 to 40 GHz
Return loss	≥ 26 dB	≥ 23 dB	≥ 20 dB
Electrical length	16.1 mm		

Mechanical Data

Number of matings	100
Weight	0.0022 kg

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MMPX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Interface - SK jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Ordering Information

Single package	33_MMPX-SK-50-1/199_NE
----------------	------------------------