

Coaxial Cable Connector 11_MCX-50-2-19/111_N

Description

Straight cable plug

Interface standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0006 kg

Environmental Data

Operating temperature	-65 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00007392
Catalogue drawing	DOU-00007394
Assembly instruction	DOC-0000181794

Ordering Information

Single package	11_MCX-50-2-19/111_NE
Bulk 100 pcs package	11_MCX-50-2-19/111_NH

Additional Information

Suitable cables	EZ_86_TP_M17
-----------------	--------------