# **Data Sheet**



# Coaxial Cable Connector 11\_BNC-50-3-4/133\_N

# **Description**

Straight cable plug

Interface standards
IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### **Technical Data**

#### **Electrical Data**

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 4 \ \text{GHz} \end{array}$ 

#### **Mechanical Data**

Centre contact crimped
Outer contact crimped
Weight 0.0103 kg

#### **Environmental Data**

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -65 °C to 165 °C compliant

#### **Material Data**

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

#### **Related Documents**

Outline drawingDOU-00006208Catalogue drawingDCA-00006196Assembly instructionDOC-0000179061

# **Ordering Information**

 Bulk 100 pcs package
 11\_BNC-50-3-4/133\_NH

 Single package
 11\_BNC-50-3-4/133\_NE

# Additional Information

Suitable cables RG\_58\_C/U, GX\_03272

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.