Data Sheet



Coaxial Panel Connector 22_BNC-50-0-2/133_N

Description

Straight bulkhead receptacle jack

Interface standards IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 4 \ \text{GHz} \end{array}$

Mechanical Data

Number of matings 500
Weight 0.0118 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00011593
Catalogue drawing	DCA-00011595
Mounting hole	DOU-00010700

Ordering Information

Single package 22_BNC-50-0-2/133_NE

Remarks

equipped with insulating washers 77 Z-0-0-2

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.