Data Sheet



Coaxial Cable Connector 11_QN-50-3-2/133_N

Description

Straight cable plug

Interface standards QN QLF compliant



Technical Data

Electrical Data

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.016 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)

-40 °C to 125 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	EPDM (Ethylene propylene diene rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

1 to 2.5 GHz

30 dB

Related Documents

 Outline drawing
 DOU-00007041

 Catalogue drawing
 DOU-00007043

 Assembly instruction
 DOC-0000181005

Ordering Information

Single package 11_QN-50-3-2/133_NE

Additional Information

Suitable cables RG_58_C/U, G_03232, GX_03272-04

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.