

Coaxial PCB Connector 82_MCX-S50-0-29/111_N

Description

Straight PCB jack

Interface Standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	surface mount
Weight	0.0004 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00012753
Catalogue drawing	DCA-00012755
Mounting hole	DOU-00012756

Ordering Information

Bulk 100 pcs package	82_MCX-S50-0-29/111_NH
Tape and Reel package	82_MCX-S50-0-29/111_NM
Single package	82_MCX-S50-0-29/111_NE