

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 46626	03/22	SEE PDM





MATERIAL:

BODY, ANTI-ROCK **RING & CONTACT:**

BERYLLIUM COPPER

INSULATOR:

PTFE

CABLE STOP:

ULTEM 1000

FINISH:

BODY, ANTI-ROCK RING & CONTACT:

GOLD OVER NICKEL

PERFORMANCE:

IMPEDANCE: FREQ. RANGE: 50 OHMS

DC TO 40.0 GHz.

MATERIAL: SEE NOTES FINISH: SEE NOTES

SURFACE AREA: N/A

PROPRIETARY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'

DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING,
3) BREAK CORNERS & EDGES 005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63-MIL-STD-10.
6) DIA: S ON COMMON CENTERS TO BE CONCENTRIC WITHIN. 005 T.I.R.
7) REMOVE ALL BURRS

DRAWN: BNK 03/11/22 SEE PDM CHECKED: APPROVED: SEE PDM



TITLE: SMP EF JACK FOR Ø.047 CABLE

1221-40115 В