

Data Sheet | Item Number: 711-402

Transformer fuse terminal block; for fuse 6.35 x 32 mm; CAGE CLAMP® connection for conductors; 22.5 mm wide; 4,00 mm²; gray

<https://www.wago.com/711-402>



Color:  gray

Electrical data

Ratings per IEC/EN

Ratings per	IEC/EN 60664-1
Rated voltage (III/2)	800 V
Rated impulse voltage (III/2)	8 kV
Rated current	10 A
Legend (ratings)	(III / 2) Δ Overvoltage category III / Pollution degree 2

Connection data

Connection points	1
Total number of potentials	1
Number of connection types	1

Connection 1

Connection technology	CAGE CLAMP®
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches

Physical data

Width	22.5 mm / 0.886 inches
Height	57.1 mm / 2.248 inches
Depth	23.5 mm / 0.925 inches

Material Data

Note (material data)

[Information on material specifications can be found here](#)

Color	gray
Fire load	0.242 MJ
Weight	13.4 g



Commercial data	
eCl@ss 10.0	27-14-11-10
eCl@ss 9.0	27-14-11-10
ETIM 8.0	EC000398
ETIM 7.0	EC000398
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918684569
Customs tariff number	85369095000

Approvals and certificates

General approvals



Approval	Standard	Certificate Name
CSA DEKRA Certification B.V.	C22.2 No. 158	1101145
UL UL International Germany GmbH	UL 1059	E45172

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 711-402	

Documentation

Additional Information			
Technical Section	03.04.2019	pdf 1949.09 KB	

CAD/CAE-Data

CAE data	
EPLAN Data Portal 711-402	
WSCAD Universe 711-402	

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com