



## RRAC3I-G

3 pole AC power inlet receptacle with D-Size mounting flange which can be mounted from the front and the rear

## **Article Variations**

Article Name	Details	Packaging	
RRAC3I-G-000-0	3/16" flat tap contacts, blue housing, power inlet	BULK	



## **Technical Information**

Product	
Title	RRAC3I-G
Connection Type	Power Connectors

Electrical		
Number of contacts	2 + PE	
Rated current per contact	16 A / 20 A RMS	
Rated Voltage	250 V / 127 V AC	
Dielectric strength (peak)	4 kV ac	
Contact resistance	$\leq$ 3 m $\Omega$	
Insulation resistance (after dampheat, IEC 68-2-30)	> 1 GΩ	

Mechanical		
Retention method	Twist lock	
Cable O.D. range	6 -15 mm	
Wiring Cable	Screw type terminals, wire size 2.5 mm <sup>2</sup> / 12 AWG	
Wiring Receptacle	Flat tabs for FASTON® (4.8 x 0.5 mm) or soldering	

Material		
Cable connector contacts	Brass, Ag plated	
Receptacle contacts	Bronze, Ag plated	
Chucks	POM	

vironmental	
Flammability	UL94 V-0
Temperature range	-30 °C to +80 °C
Protection class (mated)	IP 20
Safety Requirments	EN / IEC61984
Solderability	complies with IEC68-2-20