



2



RP2RCF Mono 1/4" right-angle plug with pan head



Article Variations

Article Name	Details	Packaging
RP2RCF	Nickel Housing, Nickel plated contacts	Plastic Packaging
RP2RCF-D	Nickel Housing, Nickel plated contacts	BULK
RP2RCF-B	Black Housing, Gold plated contacts	Plastic Packaging
RP2RCF-B-D	Black Housing,Gold plated contacts	BULK
RP2RCF-BAG	Black Housing,Nickel plated contacts	Plastic Packaging
RP2RCF-BAG-D	Black Housing, Nickel plated contacts	BULK



Technical information

Product		
Title	RP2RCF	
Connection Type	Plug	

Electrical	
Contact resistance	depends on mating connector m Ω
Dielectric strength	0.5 kV dc
Insulation resistance	> 1 GΩ

Mechanical	
Lifetime	> 1000 mating cycles
Insertion and Withdrawal force	≤ 60N
Cable O.D.	4 - 7 mm

Material	
Sleeve & Inner	Brass
Sleeve plating	Nickel
Inner plating	Nickel / Gold
Shell	Steel
Shell plating	Nickel / Black

Environmental		
Temperature range	-20 °C to +70 °C	
Flammability	UL 94 HB	
Solderability	complies with IEC68-2-20	