



## **Article Variations**

Article Name	Details	Packaging
NYS215	Stereo 3 pole, 8.2 mm distance to PCB	BULK
NYS2152	Mono 2 pole, 8.2 mm distance to PCB	BULK
NYS2152G	Mono 2 pole, gold contacts, 8.2 mm distance to PCB	BULK
NYS2152G-DI-U	Mono 2 pole, gold contacts, chrome ferrule nut, solder tap version	BULK

NYS215

3 pole horizontal 1/4" jack, all contacts switched, chrome ferrule nut



## **Technical Information**

Product	
Title	NYS215
Connection Type	Jack
Gender	female

## Electrical

Dielectric strength	0.5 kVdc
Insulation resistance	$\geq 1 \ G\Omega$
Rated current	depends on mated connector
Contact resistance	depends on mated connector

Mechanical		
Insertion force	≤ 20 N	
Withdrawal force	$\geq$ 10 N	
Lifetime	1000 mating cycles	
Wiresize		

Material	
Contact plating	SnCe
Contacts	Brass (CuZn39Pb3)
Shell / Insulation	Thermoplastic

Environmental		
Solderability	Complies with IEC 68-2-20	
Temperature range	-20 °C to +70 °C	