



NYS218

3 pole horizontal 1/4" jack, all contacts switched, extra long contacts



Technical Information

Product	
Title	NYS218
Connection Type	Jack
Gender	female

Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≥ 10 N
Lifetime	1000 mating cycles
Wiresize	

Material	
Contact plating	SnCe
Contacts	Brass (CuZn39Pb3)
Shell / Insulation	Thermoplastic

Environmental	
Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C