



NYS2202

 $2\ \text{pole}\ 1/4\text{"}\,\text{jack}$ for thick panels, long-threaded bushing with washer and nut, full metal



Technical Information

Product	
Title	NYS2202
Connection Type	Jack
Gender	female

Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≥ 10 N
Lifetime	1000 mating cycles
Wiresize	

Material	
Contact plating	SnCe
Contacts	Brass (CuZn39Pb3)
Shell	Brass (CuZn39Pb3)
Shell plating	Nickel
Insulation	Thermoplastic

Environmental	
Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C