


NYS207 Right Angle, mono 2 pole





Article Variations

Article Name	Details	Packaging
NYS207	silvery handle, black plastic cover and bushing	
NYS207-2	silvery handle, red plastic cover and bushing	



Technical Information

Product	roduct		
Title	NYS207		
Connection Type	Plug		

Electrical		
Contact Resistance	≤10mΩ	
Insulation Resistance	≥200 MΩ(Initial)	
Dielectric Strength	0.5 KVdc 50HZ	

Mechanical	
Insertion and Withdrawal Force	≤60N
Lifetime	>1,000 Mating Cycles

laterial	
Inner	Steel
Тір	Brass
Bushing	PA66+30%GF
Insulation	PVC
Front Shell	Zinc
Insulation	PA66+30%GF
Soldering Contact	Brass
Cable Clamp	Steel
Cover(Black)	PA6+30%GF
Bushing(Black)	POM
Sleeve	Brass
Тір	Nickel Plating
Front Shell	Nickel Plating
Sleeve	Nickel Plating
Inner	Zinc Plating
Soldering Contact	Tin and Cer
Cable Clamp	Tin and Cer

