

NYS224

mono 2 pole, long diecast handle



















Article Variations

Article Name	Details	Packaging
NYS224	silvery handle	
NYS224AG	gold handle, gold plated contacts	
NYS224BG	black handle, gold plated contacts	
NYS224G	silvery handle, gold plated contacts	
NYS224GT	silvery handle, gold plated contacts	
NYS224L	silvery handle with large cable outlet (8 mm)	
NYS224S	silvery handle, tip switched to ground if not inserted (silent)	



Technical Information

Product	
Title	NYS224
Connection Type	Plug

Electrical		
Contact Resistance	≤10mΩ	
Insulation Resistance	≥200 MΩ(Initial)	
Dielectric Strength	0.5 KVdc 50HZ	

Mechanical		
Insertion and Withdrawal Force	≤60N	
Lifetime	>1,000 Mating Cycles	

Material		
Tip	Brass	
Inner	Steel	
Bushing	PA66+30%GF	
Insulation	PVC	
Sleeve	Brass	
Sleeve	Zinc	
Insulation	PA66+30%GF	
Soldering Contact	Brass	
Cable Clamp	Steel	
Housing	Zinc	
Tip	Nickel Plating	
Sleeve	Nickel Plating	
Sleeve	Nickel Plating	
Housing	Nickel Plating	
Inner	Zinc Plating	
Soldering Contact	Zinc Plating	
Cable Clamp	Zinc Plating	

