

# NYS228

stereo 3 pole, long diecast handle



## Article Variations

Article Name	Details	Packaging
NYS228	silvery handle	
NYS228BG	black handle, gold plated contacts	
NYS228G	silvery handle, gold plated contacts	
NYS228GT	silvery handle, gold plated tip contacts	

## Technical Information

Product	
Title	NYS228
Connection Type	1/4" Plugs & Jacks

Electrical	
Contact Resistance	≤10 mΩ
Insulation Resistance	>200 MΩ(Initial)
Dielectric Strength	500 V dc 50HZ

Mechanical	
Insertion and Withdrawal Force	5-40N
Lifetime	>5,000 Mating Cycles

Material	
Tip	Brass
Bushing	PA66+30%GF
Insert	Brass
Sleeve	Brass
Insulation	PVC
Threaded Nut	Brass
Insulator	PA66+30%GF
Housing	Zinc
Soldering Contact	Brass
Cable Clamp	Steel
Tip	Nickel Plating
Insert	Nickel Plating
Sleeve	Nickel Plating
Threaded Nut	Nickel Plating
Housing	Nickel Plating
Soldering Contact	Tin and Cer
Cable Clamp	Tin and Cer

