



NYS225

Mono 2 pole plug with anti-kink boot and large metal handle for speaker cables









Article Variations

Article Name	Details	Packaging
NYS225	silvery handle	
NYS225B	black handle	
NYS225L	silvery handle, large cable outlet (9 mm)	
NYS225S	silvery handle, tip switched to ground if not inserted (silent) for guitar cables	



Technical Information

Product		
Title	NYS225	
Connection Type	1/4" Plugs & Jacks	

Electrical			
Contact Resistance	≤ 10mΩ		
Insulation Resistance	≥ 200 MΩ(Initial)		
Dielectric Strength	0.5 KVdc 50HZ		

Mechanical		
Lifetime	> 1,000 Mating Cycles	
Insertion and Withdrawal Force	≤ 60 N	
Cable O.D.	max 8.8 mm for standard outlet max 10 mm for large outlet (*L)	
Wiresize	12 AWG	



Material	
Tip	Brass
Bushing	PA66+30%GF
Inner	Steel
Insulation	CerPVC
Sleeve	Brass
Sleeve	
Insulation	PA66+30%GF
Soldering Contact	Brass
Cable Clamp	Steel
Housing	Zinc
Push Ring	ABS
Boot	CerPVC
Tip	Nickel Plating
Sleeve	Nickel Plating
Sleeve	Nickel Plating
Housing	Nickel Plating
Inner	Zinc Plating
Soldering Contact	Tin and Cer
Cable Clamp	Tin and Cer