

## **NYS221**

1/4" jack, long-threaded bushing with washer and nut, full metal

## **Article Variations**

Article Name	Details	Packaging
NYS221	Stereo 3 pole, special designed head for quitar stramp	



## **Technical Information**

Product		
Title	NYS221	
Connection Type	Jack	

Electrical		
Contact Resistance	≤10mΩ	
Insulation Resistance	>2,000 MΩ(Initial)	
Dielectric strength	0.5KV dc 50HZ	

Mechanical		
Insertion and Withdrawal Force	5-40N	
Lifetime	>5,000 Mating Cycles	

Material	
Jack Housing	Brass
Washer	Steel
Nut	Brass
Ground Contact	Bronze
Plastc Body	PP
Contact	Bronze
Washer	Epoxy-phenolic
Contact	Bronze
Cable Clamp	Brass
Jack Housing	Nickel Plating
Washer	Nickel Plating
Nut	Nickel Plating
Ground Contact	Nickel Plating
Contact	Tin and Cer
Cable Clamp	Tin and Cer