



and the second



RTP3C Stereo 3 pole



Article Variations

Article Name	Details	Packaging
RTP3C	nickel shell, nickel plated contacts	Plastic Packaging
RTP3C-D	nickel shell, nickel plated contacts	BULK
RTP3C-B	black shell, gold plated contacts	Plastic Packaging
RTP3C-B-D	black shell, gold plated contacts	BULK
RTP3C-BAG	black shell, nickel plated contacts	Plastic Packaging
RTP3C-BAG-D	black shell, nickel plated contacts	BULK



Technical Information

Product	
Title	RTP3C
Connection Type	Plug

Electrical	
Contact Resistance	≤10 mΩ
Insulation Resistance	>200 MΩ(Initial)
Dielectric Strength	500V dc 50HZ

Mechanical		
Insertion and Withdrawal Force	≤60 N	
Lifetime	>1,000 Mating Cycles	
Cable O.D.	2 - 4 mm	
Wiresize	0.24 mm ²	
Wiresize	24 AWG	

Material		
Sleeve Assembly	Brass	
Sleeve	Brass	
Housing	Zinc	
Sleeve Assembly	Nickel Plating	
Sleeve	Nickel Plating	
Housing	Nickel Plating	