

NYS240

Stereo 3 pole 3.5 mm cable jack



Article Variations

Article Name	Details	Packaging
NYS240	metal handle, max. cable O.D. 4 mm	Plastic Bag
NYS240BG	black metal handle, gold plated contacts, max. cable O.D. 4 mm	Plastic Bag
NYS240L	metal handle, max. cable O.D. 6 mm	Plastic Bag

Technical Information

Product	
Title	NYS240
Connection Type	Jack

Electrical	
Contact Resistance	$\leq 10 \text{ m}\Omega$
Insulation Resistance	$> 200 \text{ M}\Omega$ (Initial)
Rated Voltage	500 VAC

Mechanical	
Insertion and Withdrawal Force	$\leq 60 \text{ N}$
Lifetime	$> 1,000$ Mating Cycles

Material	
Housing	Brass
Ground Contact	Bronze
Housing	Zinc
Contact	Bronze
Contact	Bronze
Bushing	PP
Insulation	PA66+30%GF
Clamping	Steel
Insulated pipe	Steel
Housing	Nickel Plating
Contact	Tin and Cer
Contact	Tin and Cer