

NYS324

3 pole DIN chassis connector, silver plated contacts



Article Variations

Article Name	Details	Packaging
NYS324		

Technical Information

Product

Title	NYS324
--------------	--------

Electrical

Contact Resistance	<10 mΩ
Insulation Resistance	>1000 MΩ(Initial)
Dielectric Strength	500V dc
Rated Voltage	50 VAC

Mechanical

Insertion Force	≤24N
Withdrawal Force	>3N
Lifetime	>1000 Mating Cycles

Material

Housing	Aluminum
Shield	Bronze
Rivet	Brass
3 Pin Insulator	PA6+30%GF
Jack	Bronze
Housing	Nickel Plating
Shield	Silver Plating
Jack	Silver Plating