



NSB3C-20/4

Type C, length 3, 20 IN (female/send) and 4 OUT (male/return) Width: 87 mm, height: 77 mm, length: 372 mm

Supplied as disassembled set comprising of all hardware parts including plates, profiles, strain relief, end pieces and screws. Labels for channel numbering not included.



Technical Information

Product	
Title	NSB3C-20/4

Electrical	
Contact resistance	< 5 mΩ
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current per contact	2 A

Mechanical	
Cable O.D.	13 - 18 mm multicore
Insertion force	≤ 10 N
Withdrawal force	≥ 10 N
Lifetime	> 1000 mating cycles
Wiresize	0.22 and 0.14 mm ²
Wiresize	24 and 26 AWG

Material	
Shell	Aluminium
Quad plates	POM
End pieces	Thermoplastic

Environmental	
Temperature range	-25 °C to +70 °C