

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010112023](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: KK 254 Crimp Housing, High Pressure, 2 Circuits, Natural

Documents:

[3D Model](#) [Product Specification PS-7879-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[3D Model \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [7880](#)
 Application Signal, Wire-to-Board
 Overview [KK Interconnect Systems](#)
 Product Name KK 254
 Taxonomy Connector Housings
 UPC 800753612273

Physical

Circuits (maximum) 2
 Color - Resin Natural (White)
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Material - Resin Nylon
 Net Weight 0.196/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.54mm
 Pitch - Termination Interface 2.54mm
 Stackable No
 Temperature Range - Operating See Product Specification

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 7880-2B

Reference - Drawing Numbers

Product Specification PS-7879-001
 Sales Drawing SD-7880-001, SD-7880-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[7880 Series](#)

Mates With

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) KK High Pressure Crimp Terminal