

# DRS NEO 423215



Sample image

**Order symbol :** DRS NEO 423215

**Product nr :** 4850024

**Description :** DIN rail frame set

**Remarks :** 2 rows x 15 modules

**Including :**

**EAN :** 6418074312303

**El. number :**

- Finland :
- Denmark 8212054338
- Sweden :

**Dimensions :**

	Height	Width	Depth
mm :	379	279	106
inch :	14.92	10.98	4.17

**Materials :**

Material :

Base colour :

Cover colour :

Gasket material :

**Temperatures :**

Temperature °C (short term) :

Temperature °C (continuous) :

Temperature °F (short term) :

Temperature °F (continuous) :

**Rating :**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation : Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance : -

Flammability Rating :

Glow Wire Test (IEC 695-2-1) °C : C

NEMA Class

**Certificates :**