

Han Domino M12 cube (F.2)



Part number	09 14 921 2101
Specification	Han Domino M12 cube (F.2)
HARTING eCatalogue	https://b2b.harting.com/09149212101

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] Domino M12 Cube
Size of the module	Domino module
Description of the module	Large Tab

Version

Gender	Female
Number of contacts	1
Details	Please order insert separately.

Technical characteristics

Limiting temperature	-40 +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained

Page 1 / 2 | Creation date 2022-10-28 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140185272
eCl@ss	27440207 Adapter for industrial connectors (module/contact insert)