

## Han Domino Dummy cube (MF.2)



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 900 2000
Specification	Han Domino Dummy cube (MF.2)
HARTING eCatalogue	<a href="https://b2b.harting.com/09149002000">https://b2b.harting.com/09149002000</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Domino Dummy Cube
Size of the module	Domino module
Description of the module	Large Tab

### Version

Gender	Male Female
--------	----------------

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥10,000

### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances Not contained

REACH SVHC substances Not contained

## Commercial data

Packaging size 2

Country of origin Romania

European customs tariff number 85389099

GTIN 5713140185326

eCl@ss 27440392 Connector (accessories)