





NOTES:

1. Open/Short/Intermittence: 100% Testing
2. HI-POT:AC 150V 0.01S
3. Insulation Resistance: DC200V 0.01S 10MΩ Min
4. Conductive Resistance: 5Ω Max
5. Resolution Ratio: 4K*2K@60Hz
6. RoHS & REACH COMPLIANT
7. Marking: 4Kx2K(2160P) Ultra-High Definition . 3D
Cable High Speed HDMI™ Cable with Ethernet
E***** 兄 AWM STYLE 20276 80° C 30V VW-1

PIN OUT



⑦	SCREW	Philips Screw #4-40 UNC Nickel Plated L=12mm	2	PCS
⑥	NUT	Embed Nut #4-40 UNC Nickel Plated L=10mm	2	PCS
⑤	MOLDED	45P Black PVC		G
④	MOLDED	LDPE		G
③	SHEATH	HDMI2.0 Female Connector Sheath Black ABS L=11mm	1	PCS
②	CONNECTOR	HDMI2.0 Female Connector Contact Pin G/F And Shell Golden Plated	2	PCS
①	CABLE	[1P*(1/0. 32BC)+D(1/0. 32BC)+AL/MYLAR]*5C+4C*(1/0. 32BC)+AL+D(1/0. 32BC)+B(80/0. 12ALM)+BLACK PVC OD:7. 3±0. 2mm	250	MM
NO.	MATERIAL	DESCRIPTION	QTY.	UNIT

Ltemref	Quantity	Title/Name, designation, material, dimension etc			Article NO. /Reference	
Designed by		Checkde by	Approved by - date	File name	Date	Scale
ANGLE:						
UNIT:MM						
HDMI A F/F 2.0V Panel mount						
Edition					Sheet	
1					1/1	