


MIDI HIGH OUTPUT SOUNDER / BEACOI





- AC OR DC VERSIONS AVAILABLE
- I I 0dB(A) OUTPUT
- IP66 PROTECTION
- SIMPLE FIRST & SECOND FIX INSTALLATION
- FULLY INTEGRATED HIGH EFFICIENCY BEACON
- 32 ALARM TONES
- 2 STAGE ALARM



Specification

Voltage Range	AC 115Vac AC 230Vac DC 9 - 60Vdc
Current	24Vac - 40mA (typ) 230Vac - 35mA (typ) 9 - 60Vdc - 230mA (typ)
Output @ Im	I I OdB(A)
Tones	32
Alarm Stages	2
Flash Rate	lHz
Flash Power	2.5j
Temperature	- 20°C to + 70°C
Material	PC / ABS
IP Rating	IP66
Weight	0.8Kg
Body Colour	Red or Grey
Lens Colour	Red, Amber or Clear