



Machinery - Combination Saws - 305 mm Combination Saw

D27105



D27105 Features

- The next generation of TGS combination saw combines the accuracy of modern mitre saws with the power and capacity of dedicated table saws
- Brushless AC motor technology allows table and mitre saw modes to operate at different speeds optimising cutting performance
- Integral leg design increasing durability and ease of use
- 305 mm head provides an increased depth of cut of 155 mm
- New mitre and bevel adjustment systems ensure high accuracy and simple adjustment
- Additional wheels and wheel barrow mode result in the saw being extremely easy to transport around the jobsite
- Robust frame design also incorporates storage area for attachments. Unit also available in 110 Volts (1730 Max Watts with brushed motor)

D27105 Specifications

| | |
|---|---------------|
| Power Input | 2000 Watts |
| Power Output | 1700 Watts |
| Blade Speed | 4000/3000 rpm |
| Blade Diameter | 305 mm |
| Blade Bore | 30 mm |
| Bevel Capacity | 48 ° |
| Mitre Capacity [right/left] | 48/48 ° |
| Cutting Capacity at 90°/90° (W x H) | 50x155 mm |
| Cutting Capacity at 90°/90° (W x H) | 205x63 mm |
| Cutting Capacity at 45°/90° (W x H) | 45x155 mm |
| Cutting Capacity at 45°/90° (W x H) | 160x35 mm |
| Cutting Capacity at 90°/45° (W x H) | 60x110 mm |
| Cutting Capacity at 90°/45° (W x H) | 205x50 mm |
| Max. Cutting Capacity at 45°/45° | 60x100 mm |
| Max. Cutting Capacity [Sawbench position 90°/90°] | 0 - 81 mm |
| Max. Cutting Capacity [Sawbench position 90°/45°] | 0 - 56 mm |
| Weight | 40 kg |
| Depth | 800 mm |
| Length | 720 mm |
| Height | 770 mm |

D27105 Standard

- 48 tooth SERIES 60® saw blade
- Parallel fence, Riving knife
- Push stick
- Mitre dust collector
- Table saw guard
- Assembly wrench