



Cordless - Jigsaws - 36V Jigsaw

DC308KL



DC308KL Features

- Powerful DEWALT fan cooled motor with replaceable brushes and variable speed delivers fast cutting action up to 2,700 strokes per minute
- Quick and easy patented keyless blade change system accepts t-shank blades
- Tool free adjustable shoe with anti-scratch cover bevels 45 degrees in both directions
- 3-position pendulum action controls the smoothness of cuts
- Patented anti-vibration counter-balance mechanism and rubber grip provide smooth operation
- Dust blower keeps line of cut clear of chips
- Lock-off switch for added user safety
- Modular component design for trouble free servicing
- Rubber coated grip to reduce surface vibration and user fatigue
- Exclusive Nano Phosphate Li-Ion battery pack provides 2000 charge cycles, more than double that of NiCd/NiMH packs
- Battery pack produces 36 Volt power at equivalent weight to 18 Volt NiCd/NiMH pack weight

DC308KL Specifications

Voltage	36 V
Battery Capacity	Li-Ion 2.2 Ah
Power Output	550 Watts
No Load Stroke Rate	0-2700 spm
Stroke Length	26 mm
Bevel Capacity	45 °
Max. Depth of Cut [Wood]	130 mm
Max. Depth of Cut [Metal]	10 mm
Weight	3.4 kg
Length	300 mm
Height	215 mm

DC308KL Standard

- 1 hour charger
- 2 batteries
- Anti-splinter shoe insert
- Anti-scratch shoe cover
- Dust extraction adapter
- 4 blades
- Heavy duty carrying case