

## **PIGGYBACK CONNECTORS**







BU-190110035

BU-190110037

BU-190110039

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

- Mueller offers three different piggyback connectors
- Vinyl insulated
- 3 AWG sizes
  - o 12-10AWG (BU-190110039)
  - o 16-14AWG (BU-190110037)
  - o 22-18AWG (BU-190110035)
- Standard tab size .25 X .032in
- Quick connect style
- Max temperature rating of 75°C
- Voltage Rating: 300V
- All terminals are made of brass with tin plating
- Solid or stranded wire accepted
- Recommended strip length: ¼"