CP Batteries

DATA SHEET

NO MERCURY ADDED

Description: Mercury Free Alkaline Manganese Battery,

AAA Size

Chemical System : Alkaline Manganese

Nominal Voltage : 1.5 Volts

Nominal Dimensions : Ø10.5 mm x 44.5 mm

Terminals : Protruded positive(+) and flat negative(-) contacts

Jacket : Foil jacket

Applications : All electronic devices, e.g. toys, photographic

equipment, data banks, calculators, audio appliances, remote controls, paging machines.

Warranty Period : 36 months


Average Weight : 12.5g

Cross References:

GP	JIS	IEC	Eveready	Duracell	Varta
24AU	LR03	LR03	E92	MX2400	4003


Typical Service Life:


Discharge	Discharge	End Point	Service
Resistance	Condition	Voltage	Life
20 Ohms	24 Hrs/Day	0.9V	19.2Hrs



Model No.: GP24AUP







Unit: mm

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com.hk