

2 mm dia. SERIES

PATCH CORDS

This series comprises :

- **BLM patch cords** Moulded miniature extension patch cords
- **BLDM patch cords** Moulded miniature stackable patch cords

Each plug is soldered onto the cable in order to assure an excellent electrical connection with very stable transfer resistance.

CHARACTERISTICS

- Current rating max <i>PVC cable 0.3 mm² section</i>	: 5 A (at 20°C)
- Dielectric withstanding voltage	: 1 500 V rms 50 Hz
- Operating voltage	: 750 V rms 50 Hz
- Insulation resistance	: $\geq 5\ 000\ M\Omega$
- Mechanical endurance	: $\geq 10\ 000$ matings
- Average insertion loss	: 14 N
- Operating temperature	: - 40°C + 70°C

► Packaging : 10 identical patch cords.

• BLM EXTENSION PATCH CORDS

Cord length	Colour
1 : 10 cm	0 : Black
2 : 20 cm	1 : Red
4 : 50 cm	2 : Green
5 : 100 cm	3 : Blue
	4 : Yellow

R 928 0XX



• BLDM STACKABLE PATCH CORDS

Cord length	Colour
1 : 10 cm	0 : Black
2 : 20 cm	1 : Red
4 : 50 cm	2 : Green
5 : 100 cm	3 : Blue
	4 : Yellow

R 928 1XX

