

WI-M-8-XX-@

(Extra Heavy-Duty 8 AWG, Silicone Jacket Test Lead Wire)



• Mueller's WI-M-8-@ is 8 AWG, 1650/0.08 stranded, tinned copper wire with highly flexible 0.256" (6.5mm) diameter silicone jacket.

Ratings: Current 50 Amps @ 105°C

Voltage 600V Dielectric Strength 2 KV/Min Spark Test 6 KV

Bend Radius 3D

Rated Temperature -40°C to 200°C

Flammability Rating FT2

• Length: The "XX" in the model number indicated length in feet. Standard lengths: 10', 25', 30', 50', and 100'

• Color: The "@" in the model number represents color.

Available colors: -0 Black, -2 Red

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524